

Low-Decibel Fan Kits

AVFK Series

Features



- Extend the life of your rack-mount equipment by adding active cooling to your installation
- Available in kits that include one (1), two (2) or four (4) fans.
- Low-decibel for audio/visual and office environments.
- If your fans will be mounted more than 12" apart when using the kits with two (2) fans, refer to the **DNFC** Fan Cord series listed in our accessories below for a longer single connection wire.
- Fan components are recognized to UL 507 and CSA certified.
- Operating temperatures -20°C to +60°C. Relative humidity range 5% to 95% in a non-condensing space.
- Decibel (db) rating is measured at 12" to 24" from the source.
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Assembled in North America.

Part No.	Fan(s) Included	Fan Width	Total CFM	Noise (dB)	Plug Type	Maximum Fan Distance	Cord Length	Fan Guards Included
AVFK1AC120	1	4.72	58	30	NEMA 1-15P	n/a	72.00	2
AVFK2AC120	2	4.72	116	30	NEMA 1-15P	12.00	72.00	4
AVFK4AC120	4	4.72	232	30	NEMA 1-15P	12.00	72.00	8

What's Inside the Box

Qty Included	Description	Replacement Part No.
1, 2, or 4	Ball bearing type fan(s)	
2 Per fan	Chrome metal grills	DNFG
1	Cord assembly	
8 Per fan	Thread-forming 10-32 hardware	

Data subject to change without notice