

Coaxial Panel Connector 23_BMA-50-0-1/119_N

Description

Straight panel receptacle jack, flange mount

Interface standards

IEC 60169-33_MIL-STD-348A/321



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Number of matings	1000
Weight	0.0038 kg

Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Stainless Steel	
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DCA-00011187
-------------------	--------------

Ordering Information

Single package	23_BMA-50-0-1/119_NE
----------------	----------------------