

# MU10/13.SF1



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks → Solution Series

## General Information

<b>Extended Product Type:</b>	MU10/13.SF1
<b>Product ID:</b>	1SNA199012R1700
<b>EAN:</b>	3472591990126
<b>Catalog Description:</b>	MU10/13.SF1 Screw Clamp Terminal Blocks - For 5 x 20 and 5 x 25 fuses - Black
<b>Long Description:</b>	Protect your circuits with 5x20 and 5x25 fuse terminal blocks (fuse not supplied with terminal blocks).

## Ordering

<b>Color:</b>	Black
<b>Minimum Order Quantity:</b>	20 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-A screw clamp
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-A screw clamp

## Dimensions

<b>Product Net Width:</b>	13 mm
<b>Product Net Height:</b>	78 mm
<b>Product Net Depth / Length:</b>	76 mm
<b>Product Net Weight:</b>	46 g

## Technical

<b>Rated Cross-Section:</b>	10 mm <sup>2</sup>
<b>Spacing:</b>	13 mm
<b>Connection Type:</b>	Screw clamp
<b>Function:</b>	Fuse
<b>Number of Levels:</b>	1
<b>Connecting Capacity Main Circuit:</b>	Screw Clamp / Flexible 1x 0.5 ... 10 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.5 ... 16 mm <sup>2</sup>
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 16 A
<b>Rated Voltage (U<sub>r</sub>):</b>	750 V
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20

<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Wire Stripping Length:</b>	12.0 mm
<b>Recommended Screw Driver:</b>	5.5 mm
<b>Tightening Torque:</b>	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
<b>Connecting Capacity Main Circuit UL/CSA:</b>	Screw Clamp / Rigid 1x 22 ... 10 AWG
<b>Connecting Capacity UL/CSA:</b>	Stranded 10 AWG
<b>Flammability According to UL94:</b>	V0

## Environmental

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

## Certificates and Declarations (Document Number)

<b>CSA Certificate:</b>	1SND161066A0201
<b>cUL Certificate:</b>	1SND161000A0203
<b>Declaration of Conformity - CE:</b>	1SND225016U1000
<b>EAC Certificate:</b>	1SND161009A1100
<b>Environmental Information:</b>	1SND220021E1002
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-A screw clamp
<b>RoHS Information:</b>	1SND230023F0208

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000899 - Fuse terminal block
<b>ETIM 5:</b>	EC000899 - Fuse terminal block
<b>ETIM 6:</b>	EC000899 - Fuse terminal block

## Container Information

<b>Package Level 1 Units:</b>	20 piece
<b>Package Level 1 Width:</b>	172 mm
<b>Package Level 1 Depth / Length:</b>	155 mm
<b>Package Level 1 Height:</b>	71 mm
<b>Package Level 1 Gross Weight:</b>	0.92 kg
<b>Package Level 1 EAN:</b>	3472591990126

**Package Level 2 Units:** 200 piece

**Package Level 3 Units:** 4800 piece

**Product Packing Type:** Box

