

Cleaning Swabs



Description

MG Chemicals line of swabs are offered in chamois, cotton, and foam tips. The swabs are designed with a round, tapered, or rectangular tip shape that are suited for all general and precision cleaning applications.

The chamois are ideal for cleaning sensitive tape, audio, and optical heads. The cotton and foam swabs are designed for cleaning equipment, removing flux residues, applying adhesives, and absorbing chemical residues.

Features & Benefits

ESD safe—Cat No. 812AS





Non-abrasive

100 ppi medical grade head—Cat No. 812 and 8113

Low to zero lint and residue free

Can be used with IPA (isopropyl alcohol) or DI (distilled) water





Available Packaging

	Part #	Overall Length	Tip Length	Handle Length	Handle Material	Tip End	Qty per bag
Chamois Swab							
	810-15	4"	0.9"	3.2"	Plastic	Single	15
	810-50	4"	0.9"	3.2"	Plastic	Single	50
	810D-15	5"	0.9"	3.2"	Plastic	Double	15
	810D-50	5"	0.9"	3.2"	Plastic	Double	50
Double-headed Cotton Swab							
	811-100	6"	0.5"	5"	Wood	Double	100
Foam Over Cotton Swab							
	812-10	6"	0.5"	5.5"	Wood	Single	10
	812-50	6"	0.5"	5.5"	Wood	Single	50
	812-250	6"	0.5"	5.5"	Wood	Single	250
	812-100	6"	0.5"	5.5"	Wood	Single	1 000
Anti-static Foam Over Cotton Swab							
	812AS-10	6"	0.8"	5.3"	Wood	Single	10

Cleaning Swabs



Available Packaging

	Part #	Overall Length	Tip Length	Handle Length	Handle Material	Tip End	Qty per bag
Foam Swab							
	813-10	6"	0.6"	5.5"	Wood	Single	10
	813-50	6"	0.6"	5.5"	Wood	Single	50
	813-250	6"	0.6"	5.5"	Wood	Single	250
	813-1000	6"	0.6"	5.5"	Wood	Single	1 000
Rectangular Foam Swab							
	814-10	5.5"	0.9"	4.5"	Polypropylene	Single	10
	814-50	5.5"	0.9"	4.5"	Polypropylene	Single	50
	814-250	5.5"	0.9"	4.5"	Polypropylene	Single	250
	814-1000	5.5"	0.9"	4.5"	Polypropylene	Single	1 000
Tapered Cotton Swab							
	8112A-100	5.9"	0.5"	5.8"	Wood	Single	100
Cotton Tipped Application Swab							
	8113-25	3.2"	0.4"	2.5"	Polypropylene	Double	25
	8113-25000	3.2"	0.4"	2.5"	Polypropylene	Double	25 000

Disclaimer: This information is believed to be accurate. It is intended for professional end-users who have the skills required to evaluate and use the data properly. M.G. Chemicals Ltd. does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

MG Chemicals 1210 Corporate Drive Burlington, Ontario, Canada L7L 5R6 ISO 9001:2015 Quality Management System SAI Global File: 004008
 support@mgchemicals.com **North America** +(1) 800-340-0772 **International** +(1) 905-331-1396 **Europe** +44 1663 362888 **29 September 2025 / Ver. 2.0**