Data sheet

MCB 489 3P D 30A ACDC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



General ordering data

Version	Miniature circuit breaker, Characteristic curve: D, Number of poles: 3, 30 A, white
Order No.	2479210000
Type	MCB 489 3P D 30A ACDC
GTIN (EAN)	4050118490787
Qty.	24 items
Delivery status	This article will no longer be available in the future.
Available until	2025-09-01T00:00:00+02:00

Downloaded from Arrow.com.

Data sheet

MCB 489 3P D 30A ACDC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	60.3 mm	Depth (inches)	2.374 inch
Height	116 mm	Height (inches)	4.5669 inch
Width	52.9 mm	Width (inches)	2.0827 inch
Net weight	20.81 g		

Temperatures

Storage temperature		Ambient temperature	-35 °C...70 °C
Operating temperature		Humidity	40 °C / 95 % rel. humidity, no condensation

Electrical data

Voltage type	AC/DC	Rated AC voltage	480277 V
Nominal current	30 A	Interrupting capacity	10000.00 A

General data

Characteristic curve	D	Number of poles	3
Version circuit breaker	Thermomagnetic	Typical lifetime in cycles mechanical	20000
Typical lifetime in cycles electrical	6000	Type of mounting	DIN rail
Type of fixing	Rail mounting	Vibration	according to IEC 60068-2-6
Shock	according to IEC 60068-2-27	Colour	white

Classifications

ETIM 8.0	EC000042	ETIM 9.0	EC000042
ETIM 10.0	EC000042	ECLASS 14.0	27-14-19-01
ECLASS 15.0	27-14-19-01		

Downloaded from Arrow.com.