

Part Number : [936014169](#)

Product Description : Heavy-Duty Standard (STD)
Single Lever Hood, Die-cast Aluminum, with 4 Pegs,
Side Entry, Size 32A «66x40», Extended Pg29 Threaded
Fitting, High Construction, Grey

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Connectors

Engineering Part Number : 7832.4654.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771- DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Single Lever Hood, Die-cast Aluminum, with 4 Pegs, Side Entry, Size 32A «66x40», Extended Pg29 Threaded Fitting, High Construction, Grey
Component Type	Single Lever Hood
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191885346

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Component Size	32A «66x40»
Entry Location	Side
Hood Coating	Polyester Powder
Hood Color	GREY RAL 7037
Lock to Mating Part	Yes
Material - Hood	Die-cast Aluminum

Material - Peg	Stainless Steel
Net Weight	299.500/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	Pg29
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 32A «66x40» S-A and S-D Inserts

This document was generated on May 27, 2026