

Industrial Adhesives & Tapes

- Products
- Applications
- Industries
- Capabilities
- Support
- Where to Buy


[United States](#) > [All 3M Products](#) > [Manufacturing](#) > [Industrial Adhesives & Tapes](#) > [3M Tapes & 3M Adhesives](#) > [Fasteners](#) > [3M™ Hook and Loop](#) > [3M™ Fastener SJ3526N Hook Black, 1 in x 50 yd 0.15 in \(3.8 mm\) Engaged Thickness, 3 per case Bulk](#)

3M™ Fastener SJ3526N Hook Black, 1 in x 50 yd 0.15 in (3.8 mm) Engaged Thickness, 3 per case Bulk

3M ID 70070969863 UPC# 00021200862434 Part Number SJ3526N 3M Product Number SJ3526N

Print






Share



Where to Buy

Need Help?

Questions? We can help
[Contact Us](#)



View All Images

Overview	Documents
Specifications	
Adhesive Type	High Performance Rubber Adhesive
Brand	3M
Closure Life	5000
Color	Black
Engaged Thickness	0.15 Inch
Flame Retardant	No
Hook/Loop	Hook
Industries	Transportation , Specialty Vehicle , Construction , Furniture , Medical , Military & Government , General Industrial , MRO , Electronics
Length	50 Linear Yard
Length (Metric)	45.72 m
Liner Thickness	3 mil
Liner Type	White Polyethylene with Red Logo
Low Profile	No
Material	Nylon
Maximum Operating Temperature (Celsius)	49 Degree Celsius
Maximum Operating Temperature (Fahrenheit)	120 Degree Fahrenheit
Product Form	Roll
Width	1 Inch
Width (Metric)	25.4 mm