



**Part Number :** 1301060106  
**Product Description :** Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 10 Sockets with Guards NEMA 5-20 Plug, Overall Length 30.48m (100.0')  
**Series Number :** 130106  
**Status :** Active  
**Product Category :** Lamps and Lights  
**Engineering Number :** 323125



## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130106
Description	Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 10 Sockets with Guards NEMA 5-20 Plug, Overall Length 30.48m (100.0')
NEMA Configuration	NEMA 5-20
NEMA Rating	Rain Tight
Product Name	Super-Safeway
Type	String Lights
UPC	78678879885

## Agency

CSA	LR85374
-----	---------

## Electrical

Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

## Physical

Bulb Type	Incandescent
Cord Length - Primary	1.52m (5.0')
Cord Length - Secondary	1.52m (5.0')
Cord Type - Primary	12/3 SOOW
Depth	47.625mm (1.875")
Duty	Industrial
Guard Included	Yes
Guard Type	Steel
Height	107.95mm (4.250")
Lamp Type	A21
Length	30.48m (100.0')
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Stringer

Outlet	None
Packaging Type	Carton
Socket Construction	Rubber Molded

---

This document was generated on Apr 27, 2025