




NOTES:

1. ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. IEC 874-1
CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION
- 2 SC DUPLEX CONNECTORS WILL BE LEFT UNASSEMBLED AS SHOWN
INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES ≤ 5 mm
3. FILLED OUT TEST RESULT SHEET WILL BE SUPPLIED WITH EACH INDIVIDUALLY
PACKED ASSEMBLY.
- 4 BLANK LABEL
5. CABLE INFO:
 - FIBRE CORE: 50/125 μ m
 - JACKET MATERIAL: LOW SMOKE ZERO HALOGEN
 - JACKET COLOUR : ORANGE
 - OUTER DIAMETER: 2,5 x 5,0 mm
- 6 NON CROSS OVER AS PER TABLE:

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-0349565-Y	XY,0
9-0349565-1	1,5
9-0349565-9	9,5
9-0349565-0	100,0 -0/+3,0

6

LEFT CONNECTOR	RIGHT CONNECTOR
SC CONNECTOR A	SC CONNECTOR B
SC CONNECTOR B	SC CONNECTOR A

2	—	CABLE LABEL	8
4	—	DUST CAP BLACK	7
2	—	SC DUPLEX HOUSING, BEAM HALF	6
2	—	SC DUPLEX HOUSING, RET. PLATE HALF	5
4	—	SC CERAMIC OVERMOLDED	4
4	—	SC CRIMP EYELET	3
4	—	SC BOOT BEIGE	2
L	—	FOCAB 50/125S 2,5TZ ORANGE LSZH	1
Qty	Part Number	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.			
DWN 09 DEC 04 CHK 09 DEC 04 APVD 09 DEC 04		SANTHOSH. G DIWAKAR BELAVADI DIWAKAR BELAVADI	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH		PRODUCT SPEC APPLICATION SPEC WEIGHT	
MATERIAL		NAME	
—		FOMM50 LEAD 2.5TZ SC-SC DUPLEX	
—		SIZE	RESTRICTED TO
—		CAGE CODE	—
—		DRAWING NO	—
—		00779	—
—		C=349565	—
—		CUSTOMER DRAWING	—
—		SCALE	—:—
—		SHEET	1 OF 1
—		REV	E