



+ CONNECTORS

AUTOMOTIVE CONNECTOR CAPS & COVERS



✓ Active

TE CONNECTIVITY (TE)  
**SOC CONN CVR ASSY, 2POS, AMPSEAL 16, 90 DEG**  
[AMP](#) | [AMPSEAL 16](#)

2302488-2  
TE Internal Number: 2302488-2

- [EU RoHS Compliant](#)
- [EU ELV Compliant](#)
- Connector System** Wire-to-Wire
- Accessory Type** Backshell Kit
- Cable Exit Angle** 90
- Sealable** No
- Strain Relief** With

 **PRODUCT DRAWING**  
[English](#)

 **3D PDF**

DOCUMENTATION

Product Drawings

**BACKSHELL AND ELBOW KIT, 2 POSITION, PLUG ASSEMBLY, AMPSEAL 16**  
PDF  
**English**

CAD Files

**3D PDF**  
PDF  
**3D**

**Customer View Model**  
2D\_DXF.ZIP

English

Customer View Model

3D\_IGS.ZIP

English

Customer View Model

3D\_STP.ZIP

English

Product Specifications

Product Specification

108-151043

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

INSTRUCTION SHEET, AMPSEAL 16 BACKSHELLS, VERTICAL AND RIGHT ANGLE

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Wire

Accessory Type Backshell Kit

Sealable No

Strain Relief With

Configuration Features

Number of Positions 2

Body Features

Cable Exit Angle 90

Color Black

Material PA

Usage Conditions

Operating Temperature Range -40 – 125 °C [ -40 – 257 °F ]

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

**Packaging Method** Bag/Box

Other

**Serviceable** Yes

Statement of Compliance

**Statement of Compliance**

PDF