

MICRO SWITCH

FREEPORT ILLINOIS U S A
A DIVISION OF HONEYWELL INC
FED. MFG CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-7R336T

REPLACES X 85394-RZ

BZ-7R336T

M

DRAWING NUMBER

X

ISSUE

34

RELEASE NO. PR - 15400

CHECK

REVISIONS

A	C065429	J A P	4 APR 90
B	CO-89351-D	J J B	18 JUL 91
C	C0081883	J J A	27 OCT 95


CHECK

27 FEB 87

87 FEB 87

D J S 26 FEB 87


DRAWN



NOTE -
 ⚠ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE ——— 90 OZ MAX
 RELEASE FORCE ——— 7 OZ MIN
 DIFFERENTIAL TRAVEL — .004 - .009
 OVERTRAVEL ——— .005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
 S P D T

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ± .030
 TWO PLACE (.00) ± .015
 THREE PLACE (.000) ± .005
 ANGLES ±

WEIGHT .063 LB

EO-52848-B