

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301370124

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, Cord Clamp, with Cover Plates for (2) Single 20/30A Locking Receptacles



Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR6837
UL	E46237
General	
Product Family	Power Distribution
Series	130137
Enclosure Rating	NEMA 4
GFCI Reset	Manual
Mounting Style	Portable
Open Neutral Relay	N/A
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Super-Safeway
Receptacle Type	Single
Taxonomy	Power Distribution
Type	Multiple Outlet Box
UPC	78678875052
Physical	
Cord Diameter	8.26-16.64mm (.325-.655")
Cord Grip Body Size	N/A
Cord Length	N/A
Feed-Thru	No
Flip Lid	No
Material - Housing	Rubber
Number of Receptacles	1 - Customer Supplied
Packaging Type	Carton
Electrical	
Cord Type	N/A
Current - Maximum per Contact	Per Cust. Supplied Receptacle
GFCI	Yes
Ground Continuity Monitor	No
NEMA Configuration	NEMA L5-20
Voltage - Maximum	Per Cust. Supplied Receptacle
Material Info	
Engineering Number	3003

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit

Contact US

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130137 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION