650V 20A Field Stop Trench IGBT - RGW40TS65D (New)

The datasheet is coming soon.

Package



VIEW

BUY * SAMPLE * FAQ CONTACT US

* This is a standard-grade product.
For Automotive usage, please contact Sales.

PRODUCT DETAIL TECHNICAL DOCUMENTS

PART NUMBER | **RGW40TS65DGC11**
STATUS | **ACTIVE**
PACKAGE | **TO-247N**

MINIMUM PACKAGE QUANTITY | **30**
PACKING TYPE | **TUBE**
ROHS | **YES**

THIS WEBSITE USES COOKIES.
By continuing to browse this website without changing your web-browser cookie settings, you are agreeing to our use of cookies.

V_{CES} [V]	650
I_C(100°C)[A]	20
$V_{CE(sat)}$ (Typ.) [V]	1.5
tf(Typ.) [ns]	63
Built-in Diode	FRD
BV_{CES} (Min.)[V]	650
Storage Temperature (Min.)[°C]	-55
Storage Temperature (Max.)[°C]	175

RELATED PRODUCTS Other New/Updated Products Relating to RGW40TS65D

PART NUMBER	Product Series	Datasheet	Distribution Inventory
RGT20NL65D	650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	-	INQUIRY
RGT20NS65D(LPDS)	650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	-	INQUIRY
RGWX5TS65	650V 75A Field Stop Trench IGBT for the High-Speed Fast Switch	-	INQUIRY
RGWX5TS65D	650V 75A Field Stop Trench IGBT for the High-Speed Fast Switch	-	INQUIRY
RGT20NS65D(TO-262)	650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	-	INQUIRY
RGT20TM65D	650V 10A Field Stop Trench IGBT	PDF	INQUIRY

NEW PRODUCT LIST

© 1997 - 2019 ROHM CO., LTD. ALL RIGHTS RESERVED.

Downloaded from Arrow.com.