



© 2023 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G3	SUPERSEDED 364767-E	23JUL2026	SA	LET












PCB - LAYOUT PROPOSAL




TRAY PACKAGING: PACKAGING UNIT 50 PCS



TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 70 PCS






INSPECTION LEVEL 1: CONTROL CHART REQUIRED
/1 PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
/2 PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY

/3 PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3



3D VIEW
SCALE 2:1

484967-E	494068-E	SUPERSEDED 364767-E	2 REV	DESCRIPTION	ITEM NO.
1	-	-	-	TOP COVER	8
1	-	-	-	TRAY PACKAGING	7
-	1	-	-	TAPE & REEL	6
-	1	-	-	PAD	5
1	1	1	-	SOLDER CLIP LEFT	4
1	1	1	-	SOLDER CLIP RIGHT	3
5	5	5	-	PINS	2
1	1	1	-	HOUSING	1
-	-	-	REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)		
QTY			PARTS LIST		

*VERSION: WITH CUT IN, WITHOUT SEAL

1. COPLANARITY OF ALL CONTACT AND CLIPS <= 0,1MM
2 PART; 100 PCS. IN BUBBLE BAGS/BULK

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL -
-

FINISH -

DWN	B S ADRUSH	17AUG2023
CHK	M SZELAG	19AUG2023
APVD	J DE BRUIJN	19AUG2023
PRODUCT SPEC	108-94887	
APPLICATION SPEC	114-94781	
WEIGHT	-	

TE Connectivity

NAME M12 MALE, A CODE, 5P, 17MM SMT*
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-364767-E	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV G3

Downloaded from Arrow.com.