

6

5

4

3





2

1

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/31/05	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Contacts color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Current rating: 1 Amp max

Contact resistance: 20 mohms max

Insulation resistance: 5,000 Mohms min @ 500 VDC

Temperature Rating:

Operating temperature: -55°C to +105°C

Environmental:

Lead free, RoHS compliant

Positions: 4 thru 80

A = .079 [2.00] x No. of Positions per Row
B = .079 [2.00] x No. of SpacesUNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]

TOLERANCES: EXCEPT AS NOTED

INCHES: .X ± .10 ØXX ± .10

.XX ± .020 ØXXX ± .015

.XXX ± .015 ØXXX ± .010

APPROVALS

DATE

DRAWN

SS

3/31/05

CHECKED

X

SIZE

X

PART NO.

2PH2R-XX-UA

REV.

-

APPROVED

REF:

SCALE: NTS

SHEET 1 OF 1

ADAM TECH

909 Railway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.079 [2.00] DUAL ROW PIN HEADER

RIGHT ANGLE, GOLD PLATED

A

B

C

D

6

5

4

3

2

1