



Part Number : [1300910085](#)
Product Description : Woodhead Standard Duty
Reel with Flying Leads, 12/3 SJTOW Cord, 10.67m
(35.0') Cord Length
Series Number : 130091
Status : Active
Product Category : Electrical Reels
Engineering Number : 997



Documents & Resources

Drawings
[1300910085 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Electrical Reels
Series	130091
Description	Woodhead Standard Duty Reel with Flying Leads, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length
Enclosure Rating	NEMA 1
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678833608

Agency

CSA	LR29921
UL	E22769

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	120V

Physical

Bulb Included	N/A
Cable Length	0.457m (1.50')
Cable Movement	Ratchet Lock
Cord Length	10.67m (35.0')
Cord Type	12/3 SJTOW
Depth	0.30m (11.75")
Drum Lock	Ratchet

Duty	Standard
Guide Arm	2 - Position
Height	0.36m (14.25")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Net Weight	11793.392/g
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Width	196.85mm (7.750")
Wire Size (AWG)	12

This document was generated on Sep 11, 2025