

Johanson Part Number 2450AT18D0100001E

Johanson Part Number: 2450AT18D0100001E

Johanson Company: JTI

Legacy P/N: 2450AT18D0100E

Size for Capacitors (EIA): None

Description: Antennas, 1206, 2400-2500MHz, 2W, 1.5dBi (typ), Detuning resilient Edge Mount Design, Ni/Sn (RoHS), 7" Reel Embossed Tape

Specification Number: None

Life Cycle Stage: Active

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.055

Schedule B: 8529.10.60.00

Thickness (Min): 0.039

ITAR: No

End Band(Min): 0.00

ECCN: EAR99

End Band (max): 0.016

RoHS Compliance: Yes, RoHS 10/10

Standard Item: Yes

REACH: Yes

Lead Time Typical (Weeks)*: 16

Country of Origin: TW

Length (Min): 0.118

Product Family: Antennas

Length (Max): 0.134

Product Subfamily: Antennas

Width (Min): 0.055

Capacitance Value: None

Width (Max): 0.071

Cap Unit of Meas: None

Part Weight (mg): 18.48

Tolerance: None

Packaged Width (lb) Arm: None

Voltage: None

Packaging: 7" Reel Embossed Tape

Dielectric Temp Coefficient: None

Packaging Qty: 3000

Termination: 0

Operating Temp Range: -40°C to +85°C

Marking: Orientation Mark

Storage Temp Range (Packaged): -40°C to +85°C

Product Release Date: Dec. 30, 2011, 8 a.m.

Storage Temp Range (None Operating): +5°C to +35°C with RH 45% to 75%

Harmonization: 8529.10.60.00

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansontechnology.com/antennas>

Printed from: <https://www.johansontechnology.com/search/pn-detail/2450AT18D0100001E/>