



+ FIBER OPTICS

FIBER OPTIC PATCH CABLE ASSEMBLIES



✓ Active

TE CONNECTIVITY (TE)
FOMM62.5 LEAD LC/DPX ODVA - SC/DPX 300M

FullAXS | Fiber Optic , SC

8-1920985-2
TE Internal Number: 8-1920985-2

- EU RoHS Compliant with Exemptions
- EU ELV Compliant with Exemptions
- Cable Type Fiber Optic Cable (FOCAB) ODC
- Fiber Diameter (µm) 62.5/125
- Outside Cable Diameter 5.5 mm [.216 in]
- Number of Fibers 2
- Connector Color (End A) Beige

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

FIBER OPTIC LEAD 5.5 Mm LC/DPX WITH ODVA ADAPTER - SC/DPX MULTI MODE 62.5/125
PDF
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.
Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Fiber Optic Cable (FOCAB) ODC
Mode Multimode
Connector Type (End A) LC
Connector Type (End B) SC
Connector Style (End A) Duplex
Connector Style (End B) Duplex
Fiber Channel No
Product Type Cable Assembly
Cable Assembly Type LC Duplex to SC Simplex (2)

Configuration Features

Number of Fibers 2
Cable Buffering Tight Buffer
Number of Connectors (End B) 2
Number of Connectors (End A) 2

Body Features

Connector Color (End A) Beige
Connector Color (End B) Beige
Cable Color Black
Boot Type (Left) Standard
Boot Type (Right) Bend Limiting
Boot Color (Left) Black
Boot Color (Right) Beige
Ferrule Material Zirconia

Dimensions

Fiber Diameter (μm) 62.5/125
Outside Cable Diameter 5.5 mm [.216 in]

Other

Cable Assembly Length (m) 297 – 303

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF