

Search within category

GO

BUY NOW

DESIGN / INSTALL



CJK688TGGR

Keyed, Category 6, RJ45, 8-position, 8-wire universal module. Green.

Specs	Packaging Details	Documents	★ Add to Favorites	🛒 Add to BOM
Performance Level	Category 6			
Color	Green			
Module Type	Mini-Com			
Termination Style	Giga-TX (TG Style)			
Wiring Scheme	T568A/T568B			
Material	ABS/Polycarbonate			
Operating Temperature	14°F to 149°F (-10°C to 65°C)			
Storage Temperature	-40°F to 158°F (-40°C to 70°C)			
Application	Unshielded			
RoHS Compliancy Status	Compliant			
Min. Order Qty.	1			