

Part Number : [1300950282](#)

Product Description : Multi-Weave Wire Mesh Pulling Grip, Rotating Eye, Mesh Length 1.422m (56.00"), Approximate Break Strength 13879.93kg (30600 lbs)

Series Number : 130095

Status : Obsolete

Product Category : Cable Grips

Engineering Part Number : 36624



Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Cable Grips
Series	130095
Description	Multi-Weave Wire Mesh Pulling Grip, Rotating Eye, Mesh Length 1.422m (56.00"), Approximate Break Strength 13879.93kg (30600 lbs)
Comments	Color Identifier Black
Product Name	Multi-Weave
Type	Pulling Grip
UPC	78678836624

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	13879.93kg (30600 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	31.75-37.85mm (1.250-1.490")
Color - Grommet	N/A
Eye Diameter	1 5/8"
Eye Type	Rotating
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	1.422m (56.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A