FO-50360-L

| CWC6156 |
|---|
| SUPERSEDES: X115465-V7 |

| REV | DOCUMENT | CHANGED BY | CHECK |
|---|---|---|---|
| B | 0042167 | PRS 05AUG08 | BLR |




| CHARACTERISTICS | |
|---|---|
| OPERATING FORCE | 64 GRAMS MAX |
| RELEASE FORCE | 8.5 GRAMS MIN |
| DIFFERENTIAL TRAVEL | .059 MAX |
| OVERTRAVEL | .132 MIN |
| RELEASE TRAVEL | .032 MIN |

**ELECTRICAL DATA**

CONTACT ARRANGEMENT
S P D T

L215
15.1A 1/2HP 125, 250 OR 277 VAC
1/2A 125 VDC
1/4A 250 VDC; 5A 125 VAC "L"

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: [X] US(inch) CUSTOMARY [ ] SI(mm) METRIC

| | | | |
|---|---|---|---|
| NO PLACE | X | ±.040 | ±1 |
| ONE PLACE | .X | ±.030 | ±0,4 |
| TWO PLACE | .XX | ±.015 | ±0,15 |
| THREE PLACE | .XXX | ±.005 | ± |
| ANGLES | | ± | ± |

RAW MATERIAL-COMMERCIAL STANDARD

THIRD ANGLE PROJECTION

| | | |
|---|---|---|
| DRAWN | AS | 26 APR 04 |
| CHECK | AK | 26 APR 04 |

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.

DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED

PTC 2D | ASME Y14.5M-1994

**Honeywell**

TITLE
# SWITCH, BASIC

| SIZE | DWG TYPE | DRAWING NAME | REV |
|---|---|---|---|
| B | 1 | V7-7C19D8-640 | B |

SCALE NONE | WEIGHT - | SHEET 1 OF 1

Downloaded from Arrow.com.