

Part Number : 2166211031
Product Description : Squba 3.6 Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 3.60mm Pitch, Single Row, 150.00mm Length, Tin (Sn) Plating, 3 Circuits, Black
Series Number : 216621
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

2166211031_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	216621
Description	Squba 3.6 Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 3.60mm Pitch, Single Row, 150.00mm Length, Tin (Sn) Plating, 3 Circuits, Black
Application	Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Squba 3.6-to-Pigtail
Keyword	Squba 3.6
Product Name	Squba
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264746446

Electrical

Current - Maximum per Contact	14.0A
Voltage - Maximum	600V

Physical

Cable Length	150.00mm

Downloaded from Arrow.com.

Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	12.413/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	16

Mates With / Use With

Mates with Part(s)

Description	Part Number
Squba 3.6 Sealed Plug Assembly, 3.60mm Pitch, 2 Circuits, Single Row, Glow-Wire Capable, Black, UL1007/UL1061 Compatible	2077780002

Downloaded from Arrow.com.