
# PXMBNI78FPF05AFLPG135001 Datasheet

## Product Name // 5 Contacts 7/8" Front Panel Mounting Female 100mm Flying Leads

View Product Page






## // Product Description:

- 3 Contacts 7-8" Front Panel Mounting Female 0.1M Cable
- IP67 rated when mated
- Mechanical Cycles >100
- Operating Temperature -25°C to +85°C
- Rated Voltage 300 V
- ROHS compliance

## // General Information:

| | |
|---|---|
| **Product Display Title:** | 7/8" Front Panel Mounting Female 100mm Flying Leads |
| **Product Family:** | Circular Automation Connectors |
| **Product Series:** | 7/8" Series |
| **Cable Length:** | 0.1m |
| **Connection Method:** | Solder |
| **Contact Type:** | Socket Contact |
| **Current Max:** | 9A |
| **Durability:** | >100 Cycles |
| **Function:** | Front Panel Mounting Female Connector with Flying Leads |
| **Insulation Resistance:** | >100MOhm |
| **Ip Rating:** | IP67 |
| **Max Operating Temperature:** | +80°C |
| **Min Operating Temperature:** | -25°C |
| **Number Of Contacts:** | 5 Contacts |
| **Pin Layout Code:** | A Code |
| **Rohs Compliant:** | Yes |
| **Thread Size:** | PG13.5 |
| **Voltage Max:** | 300V |

## // Product PDF Links

78 Series Circular connectors...

## // Product 3D CAD Model Links

PXMBNI78FPF05AFLPG1350013D CAD...

Have a question or project enquiry you'd like to talk to us about?

Click Here To Contact Us

Downloaded from Arrow.com.