

5

4


3

2



1

Mating face according to MIL-C-24308 / DIN 41 652 / CECC 75301-802

No. 1 contact




screw locks 4-40 UNC



Printed board layout (1,6 ± 0,2 thick)
View component side
(PCB plating = Tin)

No. 1 contact



D

C

B

A

							Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub male straight 15 poles with solder pins and nuts and fitted screw locks 4-40 UNC	Maßstab/ Scale 1,5:1
						Detail.	5/03/03	S.H.			
						Insp.					
						Stand.					
09 66 221 6703	4-40 UNC	2									
09 66 221 7703	4-40 UNC	3									
09 66 221 5703	4-40 UNC	0,76 µm Au	31399	5/03/03	S.H.	HARTING EURL F-95972 Paris				TB 09 66 221 X703	Blatt/ Page 1/
Part number	nut thread	Performance level	Mod.	Dat.	Name					Sub.	

HARTING EURL
F-95972 Paris



TB 09 66 221 X703

1/