This document was generated on 08/16/2019


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1041280400

Status: Active

Overview: Wire-to-Board Connectors

Description: IllumiMate 1.00mm Pitch Wire-to-Board Crimp Housing, Single Row, Friction Lock, 4 Circuits, Natural



Series image - Reference only

Documents:

3D Model
Drawing (PDF)
Product Specification PS-104127-001-001 (PDF)
Packaging Specification PK-104128-001-001 (PDF)
RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	104128
Application	Wire-to-Board
Overview	Wire-to-Board Connectors
Product Name	IllumiMate
UPC	884982701618
Physical	
Circuits (maximum)	4
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Liquid Crystal Polymer
Net Weight	0.043/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	1.00mm
Temperature Range - Operating	-25° to +130°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-104128-001-001
Product Specification	PS-104127-001-001
Sales Drawing	SD-104128-001

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
104128 Series

Mates With
IllumiMate Header 1041270410

Use With
IllumiMate Terminal 1045398002

This document was generated on 08/16/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.