# Datasheet for part number NLDFT-3-BL-L-S120-M40A

| Our Catalog Part Number: NLDFT-3-BL-L-S120-M40A |
|---|
| Our Global Manufacturing Part Number: 078238-1613 |
| Brand: Cannon Product Category: Circular Product Line: Veam Powerlock & Snaplock Series: POWERLOCK |

| Product Datasheet | |
|---|---|
| Series | Line Drain (female contact) |
| Shell Style | Phase 3 |
| Color | Blue |
| Locking Type | Secondary Locking pin fitted to Drain Connector |
| Contact Type | 120 mm set screw |
| Cable Gland | M40A cable gland (Cable OD 19-28 mm) |
| Maximum current rating | 400 A |
| Maximum rated voltage to earth | 2KVac / 3KVdc |
| Minimum flashover | 9.5K Vdc or Ac peak |
| Operating temperature range | -30°/+125° |
| Insulation resistance | <5 M ohms @500Vdc |
| Ingress protection (mated) | IP67 |
| Protection against electrical shock | IP2X |
| Flammability | UL94-V0 |
| Contact Retention | Nylon Pin |
| Mating Method | Bayonet |
| Mating Cycles | 500 |
| Operating Voltage | 1000Vac |
| Shell Material Finish | High temperature thermoplastic |

Specifications and dimensions subject to change.



Downloaded from Arrow.com.