


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER E.O. P20044	03NOV2008		RDR
	E	REVISED PER E.O. P20392	03DEC2009		RDR
	F	REVISED PER PCN :E-18-007949	23MAY2018	DD	DM



- 3 MATERIAL: .010 [0.25] THICK COPPER ALLOY
2. WIRE RANGE: 22 AWG TO 16 AWG [0.35-1.5 mm²]
INSULATION RANGE: $\varnothing .075$ -.125 [$\varnothing$ 1.91-3.18]
- 1 APPLIES ONLY TO SELECTIVE GOLD 1060-20-0144.
INDICATED DIMENSION SHOWS GOLD PLATED AREA.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. APOSTOL 01DEC2009	TE Connectivity		
DIMENSIONS: INCHES[mm]		CHK D. MEYER 02DEC2009			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. REED 03DEC2009			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±		PRODUCT SPEC 0425-015-0000			
MATERIAL 3		APPLICATION SPEC 114-151003	NAME STAMPED CONTACT PIN SIZE 20		
FINISH SEE TABLE		WEIGHT 0.16 g	SIZE A3	CAGE CODE 4AFU8	DRAWING NO C-1060-20-01XX
CUSTOMER DRAWING		SCALE 6:1	SHEET 1 OF 1	RESTRICTED TO -	
				REV F	