





NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. SEE DRAWING HPMIMIX FOR HOLE PATTERN.
3. DIMENSIONS ARE FOR REFERENCE ONLY.




MATING FACE
ASSY: W7C81-6PG-3ES SHOWN




ASSEMBLED VIEW
ASSY: W7C81-6PG-3ES SHOWN



RECOMMENDED PANEL CUTOUT




ASSEMBLED VIEW
ASSY: W7C82-6PG-300 SHOWN



WIRING END
ASSY: W7C82-6PG-300 SHOWN

CONNECTOR P/N	POSITIONS		CONTACT STYLE	EPOXY
	#16	#20		
W7C80-6PG-300	2	4	CRIMP	(NONE)
W7C81-6PG-300			PC TAIL	(NONE)
W7C81-6PG-3ES			PC TAIL	ES
W7C82-6PG-300			SOLDER	(NONE)
W7C82-6PG-3ES			SOLDER	ES



CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

PRELIMINARY

RoHS COMPLIANT

0A		PNK		01-19-15		PDR 14001 PRELIMINARY							
REV.		INIT.		DATE		DESCRIPTION							
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXCALL CORPORATION." UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.						ORIG. DRAWN BY:		DATE:		conxcall 601 E. WILDWOOD VILLA PARK, IL 60181			
						PNK		01-19-15					
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.						CHECKED BY:							
						APPROVED BY:							
UNLESS OTHERWISE SPECIFIED TOLERANCES: 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16 = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX						SCALE		SIZE		SHEET		TITLE: PANEL-MOUNT CONNECTOR 2-16 + 4-20 PIN CONTACTS MINI-CON-X POWER/SIGNAL	
						NTS		B		1 OF 1			
						▽						FILE:	
W7C8X-6PG-3XX_CD		SLW											
						PART NUMBER:				W7C8X-6PG-3XX_CD		REV 0A	