Desktop Computer AC Power Cable, NEMA 5-15P to C13 - 10A, 125V, 18 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: **P006-010**







Computer power cable allows you to connect your PC, printer or monitor into a surge protector, PDU or UPS with a NEMA 5-15R outlet.

Features

Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment This computer power supply cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- NEMA 5-15P to C13 extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect devices like computers, printers and monitors to a PDU up to 10-ft. (3.05 m) away in your workstation
- Extend an existing power connection up to 10-ft. (3.05 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P006-010 NEMA 5-15P to C13 Computer Power Cable, 10-ft. (3.05 m), Black

Specifications

OVERVIEW	
UPC Code	037332164780
Product Type	Computer Power Cord
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
Connector Style	Straight

Downloaded from Arrow.com.

PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm²)	0.82
Power Cord Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.10
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 0.25
Shipping Weight (lbs.)	0.72
Shipping Weight (kg)	0.33
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
Locking Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	

Downloaded from Arrow.com.

Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.