









Max. Temperature: 260° during 10 seconds.

0955 455 3621 741	1	M3	Black insulator	Reel Packaging: 140 connectors (See details on page2/2)				
0955 455 3622 741	1	4-40 UNC						
0955 455 6621 741	2	M3						
0955 455 6622 741	2	4-40 UNC						
0955 455 7621 741	3	M3						
0955 455 7622 741	3	4-40 UNC						
Part number	PL	Screw lock	Index designation					
 All Dimensions in mm Original Size DIN A 3			Techn. Character.		Free size tolerances			
				Dat.	Name	Scale	D-Sub SMT, 37 poles Female, Straight with screw locks and ground pins	
			Detail.	25-Oct-11	Johnson.S	1.5:1		
			Insp.	17-Nov-11	Steven.W			
			Stand.	17-Nov-11	Steven.W			
EC04070	17-Nov-11	Johnson.S	Zhuhai HARTING Limited				TB 09 55 455 x62x	Page 1/2
Mod.	Dat.	Name					Sub.	



Detail A



See TB 09 55 455 x62x folio 1/2
for connector dimensions
and PCB layout

Packaging in accordance with
EIA 481-2.

0955 455 3621 741	1	M3	Black insulator	Reel Packaging: 140 connectors
0955 455 3622 741	1	4-40 UNC		
0955 455 6621 741	2	M3		
0955 455 6622 741	2	4-40 UNC		
0955 455 7621 741	3	M3		
0955 455 7622 741	3	4-40 UNC		
Part number	PL	Screw lock	Index designation	

 All Dimensions in mm Original Size DIN A 3			Techn. Character.			Free size tolerances			
				Dat.	Name	Scale	D-Sub SMT, 37 poles Female, Straight with screw locks and ground pins		
			Detail.	25-Oct-11	Johnson.S				
			Insp.	17-Nov-11	Steven.W				
			Stand.	17-Nov-11	Steven.W				
			Zhuhai HARTING Limited 			TB 09 55 455 x62x			Page 2/2
EC04070	17-Nov-11	Johnson.S				Sub.			
Mod.	Dat.	Name							