650V 25A Field Stop Trench IGBT - RGW50TS65D (New Product)

The datasheet is coming soon.

BUY * FAQ CONTACT US

Package



* This product is a standard grade product. This product is not recommended for use in car equipment.

MAIN SPECIFICATION TECHNICAL DATA

PART NO. | RGW50TS65DGC11
STATUS| SUPPLY
PACKAGE | TO-247N
NUMBER OF UNITS | 450
MINIMUM PACKAGE QUANTITY | 30
PACKING FORM | TUBE
ROHS | YES

SPECIFICATION:

Series
W: High speed fast SW
IN $_{CES}$ [V]
650
I_C(100°C)[A]
25
$V_{CE\ (sat)}$ (Typ.) [V]
1.5
tf(Typ.) [ns]
53
Built-in Diode
FRD
BV_{CES} (Min.) [V]
650
Storage Temperature (Min.)[°C]
-55
Storage Temperature (Max.)[°C]
175

FEATURES:

N/A

RELATED PRODUCTS Other new/current related products RGW50TS65D

PART NUMBER	Product Series	Datasheet	Distribution Inventory
RGT20NL65D	650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	-	INQUIRE
RGT20NS65D(LPDS)	650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	-	INQUIRE
RGWX5TS65	650V 75A Field Stop Trench IGBT for the High-Speed Fast Switch	-	INQUIRE
RGWX5TS65D	650V 75A Field Stop Trench IGBT for the High-Speed Fast Switch	-	INQUIRE
RGT20NS65D(TO-262)	650V 10A Field Stop Trench IGBT for the inverter (tsc 5us)	-	INQUIRE
RGT20TM65D	650V 10A Field Stop Trench IGBT	PDF	INQUIRE

NEW PRODUCT LIST

© 1997 - 2019 ROHM CO., LTD. ALL RIGHTS RESERVED.
Downloaded from Arrow.com.