

YOUR SELECTED PRODUCT

For other versions than the listed available standard types, please contact PRECI-DIP

- SPECIFICATIONS:**
- Socket contact without solder tail / SMD socket contact
- Materials: body brass, contact clip BeCu
 - Electrical contact resistance max. 15 milliohms
 - Mechanical life min. 500 cycles

AVAILABLE STANDARD TYPES

Ordering Part Number		Plating Body	Plating Clip	Insertion	Extraction	Dia.Gauge	Max Current
01401-13-3010	RoHS	0.25µm Au	0.75µm Au	2.00 N	1.00 N	0.43 mm	3.0 A
01401-83-3010	RoHS	5µm Sn	0.75µm Au	2.00 N	1.00 N	0.43 mm	3.0 A
01401-87-3010	RoHS	5µm Sn	Flash Au	2.00 N	1.00 N	0.43 mm	3.0 A
01401-13-3110	RoHS	0.25µm Au	0.75µm Au	0.70 N	0.40 N	0.46 mm	3.0 A
01401-93-3110		5µm SnPb	0.75µm Au	0.70 N	0.40 N	0.46 mm	3.0 A

[May 2008] PRECI-DIP participation to exhibition 'Arrow Global Village' in Helsinki (Finland)

More >>

[April 2008] PRECI-DIP SA and its local distributor SEMICON

<< Back