Part Number : 1301460129
Product Description : Watertite Extreme Receptacle with Single Flip Coverplate, 2 Pole/3 Wire, NEMA 5-15, 125V
Series Number : 130146
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 60W47



Documents and Resources

Drawings

1301460129_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130146
Description	Watertite Extreme Receptacle with Single Flip Coverplate, 2 Pole/3 Wire, NEMA 5-15, 125V
IP Rating	IP67
NEMA Configuration	NEMA 5-15
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871402

Agency

CSA	LR6837
UL	E68122

Electrical

Current - Maximum per Contact	15.0A
GFCI	No
Voltage - Maximum	125V

Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes
Gender	Female

Downloaded from Arrow.com.

Length	N/A
Lighted Connector	No
Locking Blade	No
Net Weight	12.440/g
Poles	2-pole/3-wire
Receptacle Type	Single

Downloaded from Arrow.com.