



Part Number : [1300950167](#)

Product Description : Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Mesh Length 0.457m (18.00"), Approximate Break Strength 2494.76kg (5500 lbs)

Series Number : 130095

Status : Active

Product Category : Cable Grips

Engineering Number : 35932



Documents & Resources

Drawings

[1300950167_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Cable Grips
Series	130095
Description	Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Mesh Length 0.457m (18.00"), Approximate Break Strength 2494.76kg (5500 lbs)
Product Name	Medium Duty
Type	Pulling Grip
UPC	78678835932

Agency

CSA	LR32159
-----	---------

Physical

Approximate Break Strength	2494.76kg (5500 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	19.05-25.15mm (.750-.990")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.508m (20.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A