molex



Part Number : 39000219
Product Description : Mini-Fit Male Crimp Terminal, 0.76µm Selective Gold (Au) Plated Phosphor Bronze, 24-18 AWG, Reel
Series Number : 5558
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : 5558PBGS
Packaging Alternative : 39000220 (Bag)

Documents and Resources

Drawings

039000219_sd.pdf

55580001-PK-000.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

55560001-AS-000.pdf

55560002-AS-000.pdf

55560002-PS-CH-000.pdf

55560002-PS-ES-000.pdf

55560002-PS-SK-000.pdf

55560008-TS-000.pdf

PS-5556-001-001.pdf

PS-5556-002-001.pdf

55560001-TS-000.pdf

55560010-TS-000.pdf

TS-5556-002-001.pdf

Product Environment Compliance

Compliance

Downloaded from Arrow.com.

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5558
Description	Mini-Fit Male Crimp Terminal, 0.76µm Selective Gold (Au) Plated Phosphor Bronze, 24-18 AWG, Reel
Application	Power, Wire-to-Wire
Product Name	Mini-Fit
UPC	800754396349

Electrical

Downloaded from Arrow.com.

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	126.914/mg
Packaging Type	Reel
Plating min - Mating	0.760µm
Plating min - Termination	2.032µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size (AWG)	18, 20, 22, 24
Wire Size mm^2	N/A

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit Jr. Plug Housings	5559
Mini-Fit BMI Dual Row Plug Housings	42475
Mini-Fit Jr. Dual Row Plug Housings	46993

Application Tooling

Global

Description	Part Number

Downloaded from Arrow.com.

Extraction Tool for Mini-Fit Jr. Terminals	11030044
FineAdjust Applicator for Mini-Fit Crimp Terminals, Double 22+22 AWG	2037026300
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 24-18 AWG	638190901
FineAdjust Applicator for 20-18 AWG and 24-18 AWG Wires with Insulation Diameter 1.90-2.30mm	639015600
FineAdjust Applicator for Insulation OD 1.40-1.70mm - 24-18 AWG	639023900
FineAdjust Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	639024800
FineAdjust Applicator for Insulation OD 2.30-2.60mm - 24-18 AWG	639024900
FineAdjust Applicator for Insulation OD 2.50-2.95mm, 24-18 AWG	639047800
FineAdjust Applicator for Insulation OD 1.65-2.05mm, 24-18 AWG	639048000
T2 Terminator for Insulation OD 1.90-2.30mm - 24-18 AWG	639115600
T2 Terminator for insulation OD 1.40-1.70mm - 24-18 AWG	639123900
T2 Terminator for insulation OD 2.50-2.95mm optimized for 18 AWG only	639124800
T2 Terminator for insulation OD 2.30-2.60mm - 24-18 AWG	639124900
T2 Terminator for Mini-Fit Crimp Terminals, 24-18 AWG with Large Insulation ODs	639147800
T2 Terminator for Mini-Fit Crimp Terminals, 24-18 AWG with Smaller Insulation ODs	639148000

Downloaded from Arrow.com.

Downloaded from Arrow.com.