



Part Number : [430300008](#)

Product Description : Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Bag

Series Number : 43030

Status : Active

Product Category : Crimp Terminals

Packaging Alternative : [430300002](#) (Reel)



Documents and Resources

Drawings

[430300008 sd.pdf](#)

[PK-43030-003-001.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[430450001-AS-000.pdf](#)

[430450001-PS-KO-000.pdf](#)

[430450001-PS-SP-000.pdf](#)

[PS-43045-001.pdf](#)

[430450005-TS-000.pdf](#)

[430450006-TS-000.pdf](#)


[430450007-TS-000.pdf](#)

[TS-43045-001-001.pdf](#)

[TS-43045-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006

EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	43030
Description	Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 24-20 AWG, Bag
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Micro-Fit 3.0
UPC	800754369299

Electrical

Current - Maximum per Contact	7.0A
-------------------------------	------

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.094/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size (AWG)	20, 22, 24
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Receptacle Housings	<u>43025</u>
Micro-Fit 3.0 Single Row Receptacle Housings	<u>43645</u>
Micro-Fit BMI Dual Row Receptacle Housings	<u>44133</u>
Micro-Fit BMI Single Row Receptacle Housings	<u>46623</u>
Micro-Fit TPA Single Row Receptacle Housings	<u>171850</u>
Micro-Fit TPA Receptacle Housings	<u>172952</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	<u>11030043</u>
Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 30-20 AWG	<u>638120800</u>
PremiumGrade Hand Crimp Tool for Micro-Fit 3.0 Terminals, 30-20 AWG	<u>638190000</u>

This document was generated on May 27, 2026