

Product Line

DeepTronica

>

Single Pair Ethernet

>

ZConnect

>

Ceres

>

X-Lok

>

M Series

>

Accessory

M5

Guided M8

M8

M10.5

M12 (A)

M12 (B)

M12 (D)

M12 (I)

M12 (K)

M12 (L)

M12 (S)

M12 (T)

M12 (X)

M23

FLOS & FLOS+

>

Power

>

RBL

>

HS-Lok

>

NMEA 2000

>

Heavy Duty Shielded

>

RJ

>

USB

>

SSL

>

HDMI

>

DVI

>

Fiber Optic

>

RF

>

Cable Joiner

>

Cable Gland

>

Pressure Relief Vent

>

LED Light Guide

>

D-Sub

>



M12A12FL-12AFL-SD002

Operating Temperature: -20°C ~ +80°C

Transmission Speed: N/A

Shielded: Metal, Non-shielded

Jacket Material: PVC

Certificate: UL1977, UL2238, UL1863

You must login first for view the price

Quantity

- 1 +

Check Stock

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

M Series....
CAP-WBDF SMA1
-40°C ~ +105°C

-

0

+

M Series....
CAP-WBDF SMA2
-40°C ~ +105°C

-

0

+

M Series....
CAP-WBDF SPB1
-40°C ~ +105°C

-

0

+

M Series....
IA-A12M-A12M-...
-20°C ~ +85°C

-

0

+

M Series, M12, A...
M12A-12BMMA-...
-40°C ~ +105°C

-

0

+

M Series, M12, A...
M12A-12BMMA-...
-40°C ~ +105°C

-

0

+

Add to Cart

Inquiry

Specifications		Download / CAD	
Nominal Current		Connector Type	
1.5A		Overmolded	
Shielded		No. of Contacts	
Metal, Non-shielded		12	
Connector Gender		Backshell	
Female		Straight	
Mating Style		IP Rating	
Screw Thread		IP68	
Assembly Style			
N/A			
<div><div></div><div>More Options</div></div>			

People Also Bought

