# Datasheet for part number DEMAMY-15S-F0

| Our Catalog Part Number: DEMAMY-15S-F0 |
| --- |
| Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*MA |

| Product Datasheet | |
| --- | --- |
| General | D*M High reliable D-Sub Connectors with crimp termination |
| Wire Gauge Range AWG | Standard: AWG 20-28. High Density: AWG 22-28 |
| Mating Cycles | 500 |
| Contact Arrangement | Standard: 15 contacts size 20. High Density: 15 contacts size 22 |
| Dielectric Withstanding Voltage | 1000 VAC at sea level |
| Current Rating | 7.5 A max |
| Contact Resistance | 10 milli Ohm max |
| Operating Temperature | -55°/+150° |
| Salt Spray Test | 48 hours {96 Hrs for Stainless Steel} |
| Shell Material | steel |
| Shell Finish | Yellow chromate over zinc |
| Insulator Material | Thermoplastic, type PCT UL 94V-0 |
| Insulator Color | white |
| Gender | Socket |
| Contacts | delivery without contacts, please order separately |
| Contact Type | Crimp |
| Contact Material | copper alloy |
| Contact Finish | gold over nickel (Performance Class 2) |
| Hardware | Dual Float Mount |

Specifications and dimensions subject to change.



Downloaded from Arrow.com.