
Part Number : 510481600
Product Description : 2.00mm Pitch Cable Holder, Vertical, Low Profile, for Ribbon Cable, 16 Circuits
Series Number : 51048
Status : Obsolete
Product Category : Connector Housings



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

Obsolete

Downloaded from Arrow.com.

General

Status	Obsolete
Category	Connector Housings
Series	51048
Description	2.00mm Pitch Cable Holder, Vertical, Low Profile, for Ribbon Cable, 16 Circuits
Component Type	One Piece
Product Name	Board-in,Cable Holder
UPC	800753574885

Electrical

Voltage - Maximum	N/A

Physical

Circuits (Loaded)	16
Color - Resin	Natural
Entry Angle	Vertical
Glow-Wire Capable	No
Lock to Mating Part	No
Material - Plating Mating	N/A
Material - Resin	Nylon
Net Weight	332.300/mg
Number of Rows	1
Packaging Type	Bag
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	N/A
Polarized to PCB	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	Ribbon Cable
Wire Insulation Diameter	1.60mm max.
Wire Size (AWG)	26

Obsolete

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Topcoated Ribbon Cable

This document was generated on Sep 17, 2026

Obsolete

Downloaded from Arrow.com.