

Configuration details V901CCV (AC input)

|                              |                                                        |
|------------------------------|--------------------------------------------------------|
| Part number                  | V901CCV                                                |
| Product Description          | V9FSLF 15C3SN 15C3SN 24C5SN 5/5H1H/1HSN W5FSV4         |
| Total requested output power | 920 W                                                  |
| Total output power           | 900 W                                                  |
| Approvals                    | C-UL-US, CE.                                           |
| Cooling                      | Forward air fan - end mount                            |
| Input                        | Screw                                                  |
| Earth leakage                | 290 microamps maximum leakage current                  |
| Primary option               | AC fail with PSU + fan inhibit and 5V/100mA aux supply |
| Dimensions                   | Length: 268.4mm, Width: 126.5mm, Height: 62.8mm        |

- Notes
- 1. Caution: Total connected power (920W) exceeds total available power (900W). You will not be able to use all outputs at maximum rating simultaneously.
  - 2. W5FSV4 wide range modules have a range of 0.25 - 32 Vdc with a current capability of 8.5 A.

|            |                                                          |                                       |                                                      |                                                      |                                                      |
|------------|----------------------------------------------------------|---------------------------------------|------------------------------------------------------|------------------------------------------------------|------------------------------------------------------|
| Module     | W5FSV4                                                   | H1H/1H                                | C5                                                   | C3                                                   | C3                                                   |
| Output 1   | 5V/8A                                                    | 5V/12A                                | 24V/10A                                              | 15V/18A                                              | 15V/18A                                              |
| Output 2   | -                                                        | 5V/8A                                 | -                                                    | -                                                    | -                                                    |
| Option     | 0-5V programming, current programming, enable, fixed ovp | Inhibit, module good and remote sense | Inhibit, module good, remote sense and current share | Inhibit, module good, remote sense and current share | Inhibit, module good, remote sense and current share |
| Connection | Screw                                                    | Screw                                 | Screw                                                | Screw                                                | Screw                                                |

The view shown is of the output end of the supply.

Request a quote