

4-Port USB-C Charger, 72W, 1x USB-C PD Port (60W) and 3x USB-A Auto-sensing ports

MODEL NUMBER: **U280-004-WS3C1**



Charges up to 4 electronic devices at the same time via USB connection. Recommended for charging mobile devices ranging from smartphones and tablets to larger power consumers, such as MacBooks and Chromebook Pixels.

Description

Whether you're at home or in the office, Tripp Lite's U280-004-WS3C1 4-Port USB Charging Station provides enough ports and power to keep your devices at 100% capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. You can charge up to four tablets, cell phones, laptops and other devices at the same time. The U280-004-WS3C1 doesn't require a computer, so you can take it anywhere AC power is available.

The U280-004-WS3C1 features three auto-sensing USB-A ports, each capable of delivering up to 5V, 2.4A, which is enough for charging cell phones, tablets and other mobile devices. Each USB-A port senses the connected device and automatically adjusts the required power level accordingly. A USB-C port supports power output up to 20V, 3A for charging more battery-intensive USB power delivery devices, such as a MacBook®, MacBook Pro® or Chromebook Pixel™.

To charge your USB devices, simply connect the detachable four-foot power cord's NEMA 1-15P plug to an AC power outlet, and connect your devices to the available USB ports. The unit protects against overheating, overcurrent and overcharging—in fact, it stops charging as soon as your devices' batteries are at full capacity.

Highlights

- USB-A auto-sensing ports each support up to 5V, 2.4A for charging
- USB-C port supports up to 20V, 3A for charging
- Internal dual-voltage power supply with NEMA 1-15P plug
- Protects against overheating, overcurrent and overcharging
- No computer required

System Requirements

- The U280-004-WS3C1 includes a C7 to 1-15P power cord for use in 120V applications. An applicable 230V power cord can be purchased separately for use in 230V applications.

Package Includes

- U280-004-WS3C1 4-Port USB Charging Station
- C7 to NEMA 1-15P power cord, 4 ft.
- Quick Start Guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Features

Charges Up to 4 Devices at the Same Time

- Recommended for charging tablets, cell phones, laptops and other devices at home or office
- Functions anywhere AC power is available—no computer required

Provides Plenty of Juice for Charging

- USB-A auto-sensing ports each support up to 5V, 2.4A for charging
- Senses connected USB-A devices and automatically adjusts required power level
- USB-C port supports up to 20V, 3A for charging more battery-intensive devices, such as laptops
- Protects against overheating, overcurrent and overcharging

Easy to Use

- Internal dual-voltage power supply with NEMA 1-15P plug and detachable 4 ft. cord
- No computer required

Specifications

OVERVIEW	
UPC Code	037332196507
Product Type	Plug in Charger
Charging Form Factor	Charging Hub
Device Compatibility	Phone; Tablet; Amazon Kindle
Over Current Protection	Yes
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Input Connection Type	IEC C7
Plug Type	C7 to NEMA 1-5P
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50/60Hz
Input Plug Type	NEMA 1-15P (NON-POLARIZED)
Input Current	5V (2.4A) / 20V (3A)
OUTPUT	
Output Capacity	USB-A: 5V 2.4A; USB-C: 20V 3A
Overload Protection	Yes
CHARGING	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Charging Ports / Amps	(3) 2.4A; (1) 3A / 2A / 1.5A
Number of Charging Ports	4
Overcharge Protection	Yes
Total Charging Amps	5.4A
USB Power Delivery (PD) Charging Support	Yes
Charging Method	USB
Total Charging Watts	72
USB Power Delivery (PD) Charging Specification	3.0
Charging Ports Detail	USB-C: 20V 3A (60W), PD 3.0USB-A: 5V 2.4A (12W)
Charging Port Type	(3) USB A (FEMALE); USB C (FEMALE)
PHYSICAL	
Color	Black
Material of Construction	Polycarbonate
Shipping Dimensions (hwd / cm)	4.06 x 16.26 x 12.95
Shipping Dimensions (hwd / in.)	1.60 x 6.40 x 5.10
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
Unit Dimensions (hwd / cm)	9.1 x 7.6 x 2.8
Unit Dimensions (hwd / in.)	3.6 x 3.0 x 1.1
Unit Weight (kg)	0.22
Unit Weight (lbs.)	0.49
ENVIRONMENTAL	
Operating Temperature Range	32°F to 104°F / 0°C to 40°C
Storage Temperature Range	-4°F to 176°F / -20°C to 80°C
Relative Humidity	5% to 90% RH, NON-CONDENSING
Power Consumption (Watts)	72W
CONNECTIONS	
Ports	4
Side A - Connector 1	NEMA 1-15P (NON-POLARIZED)
Side B - Connector 1	(3) USB A (FEMALE)
Side B - Connector 2	USB C (FEMALE)
FEATURES & SPECIFICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Technology	USB
SPECIAL FEATURES	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
STANDARDS & COMPLIANCE	
Certifications	FCC, WEEE, EAC, CE, UL, IEC, RoHS, REACH
Approvals	UL Listed
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>