



All Categories 



Polyimide label roll

Part Number: THT-97-728-10

Product Number: 139899

Size: 0.500" W x 0.200" H (12.700 mm W x 5.080 mm H)

Material Description: Permanent Polyimide

QTY/UOM: 10,000/Roll

Overview	Specifications
Specifications for Polyimide label roll	
Part Number	THT-97-728-10
Acceptable Ribbon Series	4800
Adhesive	Permanent Acrylic
After Process	Yes, this material will work with this application
Agency Approval(s)/Compliance	UL Recognized, MIL-STD-202F, Notice 12, Method 215J
Application	Circuit Board ID, Component ID
Board Application	SMT - Top/Bottom, Through Hole - Bottom, Through Hole - Top
Brady Material Number	B-728
Brand	UltraTemp Series
Color	White
Description	Polyimide label roll
Finish	Matte
Height (in)	0.200"
Height (mm)	5.080 mm
Label Type/Style	Label
Material Description	Permanent Polyimide
Material Type	Polyimide
Printable Area (in)	0.500" W x 0.200" H
Printable Area (mm)	12.700 mm W x 5.080 mm H
Printer Compatibility	Thermal Transfer Printers
Product Number	139899
Qty Per Row	1
QTY/UOM	10,000/Roll
Recommended Ribbon Series	R6000
Size	0.500" W x 0.200" H (12.700 mm W x 5.080 mm H)
Special Properties	Excellent resistance to harsh fluxing and wave solder environments, Resists all commonly employed methods of cleaning
Suggested Ribbon Part#	R6011
Surface Mount Technology (SMT)	Yes, this material will work with this application
Through Hole Technology	Top: Yes, Bottom: Yes
UPC Code	75447393466
Vertical Repeat	0.300" (7.62 mm)
Web Width	0.700" (17.78 mm)
Width (in)	0.500"
Width (mm)	12.700 mm
RoHS Compatibility	Pass 2011/65/EU