


NOTES:

MATERIAL

1. Insulator Material: PBT+30%GF(UL94V-0), Grey
2. Contact Material : Brass
3. Contact Plating : Tin Over Ni

ELECTRICAL

- 1.Current Rating : 3AMP
2.Withstand Voltage : 500V AC/Minute
3.Contact Resistance : 20mΩ max



4. Insulation Resistance: 1000MΩ min

ENVIRONMENTAL

- 1.Operation Temperature: -40°C to +105°C
2.Packing : Tray packing

Order information:

xx : 06,08,10,12,14,16,18,20,24
26,30,34,40,50,60,64



Dimension antitheses list	
NO. Pin	L
6P-8P	4.00
10P-64P	4.40

RoHS compliant

Scale	1:1						Date	Name
TOLERANCE						Drawn	29.12.2009	Dean
X.X	±0.40					Approved	29.12.2009	Hellwig
X.XX	±0.25							
X.XXX	±0.15							
DIM	TOL							
Angle	±3°							
		①	Drawn	29.12.2009	Dean			
		Id.	Modification	Date	Name			

Customer-No.

ASSMANN WSW-No.

AWHW xxG-0502-T

Drawing-No.

ASS 4009 CO

rev01

Replace

Sheet