

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0357450110

Status:

Active

Overview:

VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Male Crimp Terminal, 20-22 AWG, Type A



Series image - Reference only

Documents:	
Drawing (PDF)	Application Specification 351500000ASENG-000 (PDF)
3D Model (PDF)	Application Specification 351500000ASKOR-000 (PDF)
3D Model	Packaging Specification PK-35745-001-001 (PDF)
Product Specification 351800400-001 (PDF)	Datasheet (PDF)
Product Specification 351800600-001 (PDF)	Brochure (PDF)
Product Specification PS-35150-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	35745
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	800754378406
Physical	
Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.280/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.60mm max.
Wire Size AWG	20, 22
Wire Size mm²	0.30-0.50
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Crimp Specification	CS-35745-001-001
Packaging Specification	PK-35745-001-001
Product Specification	351800400-001, 351800600-001, PS-35150-001-001
Sales Drawing	SD-35745-001-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

35745 Series

Use With

VersaBlade Standard Receptacle Housings [35150](#)
VersaBlade Standard Plug Housings [351510310](#) , [351510314](#) , [351510319](#) , [351513319](#) , [351514319](#) , [351510410](#) , [351510412](#) , [351510414](#) , [351510419](#) , [351513419](#) , [351514419](#) , [351510610](#) , [351510612](#) , [351510614](#) , [351510619](#) , [351513619](#) , [351514619](#)
VersaBlade Multi-Module Receptacle Housings [35180](#) , [35524](#) , [2026500909](#) , [2041020609](#) , [2041020429](#)
VersaBlade Multi-Module Plug Housings [351810210](#) , [351810214](#) , [359659210](#) , [359659213](#) , [2041020409](#) , [2041020419](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction and Activation Tool	<u>638132700</u>
Hand Crimp Tool for Industry standard 1.78mm Terminals	<u>638196800</u>
T2 Terminator Die	<u>638529000</u>
FineAdjust Applicator	<u>638629000</u>
FineAdjust Applicator for VersaBlade .070	<u>639042200</u>
Male and Female Terminals, 20-22 AWG	

This document was generated on 08/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION