

Adapter - HC-NPT-1/2-M20 - 1686847

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



NPT adapter, IP68, up to 5 bar, incl. O-ring seal, M20 to 1/2"



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 822705
GTIN	4017918822705
Weight per Piece (excluding packing)	34.440 g
Custom tariff number	74199990
Country of origin	Germany

Technical data

Dimensions

Length	25 mm
Length without connecting thread	18.5 mm
Connecting thread diameter	20 mm
Length of the connecting thread	6.5 mm

Ambient conditions

Degree of protection (IP)	IP68 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material	Brass, nickel-plated
O-ring material	NBR

Adapter - HC-NPT-1/2-M20 - 1686847

Technical data

General

Thread type on connection side	M20
Thread type on seal side	1/2-inch NPT
Color	silver


Environmental Product Compliance

	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Adapter - HC-NPT-1/2-M20 - 1686847

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27149100
eCl@ss 6.0	27149100
eCl@ss 7.0	27439207
eCl@ss 8.0	27439207
eCl@ss 9.0	27430314

Adapter - HC-NPT-1/2-M20 - 1686847

Classifications

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000938
ETIM 6.0	EC000938
ETIM 7.0	EC000938

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------