

Part Number : 1200661016
Product Description : Micro-Change (M12) Double-Ended Cordset, 4 Poles, A-Coded, Male (90°) to Female (Straight), 18 AWG, Yellow TPE Cable, 4.0m (13.12') Length
Series Number : 120066
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 884032K03M040

Documents and Resources

Drawings

1200661016_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset, 4 Poles, A-Coded, Male (90°) to Female (Straight), 18 AWG, Yellow TPE Cable, 4.0m (13.12') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78678842389

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	7.14mm (.281")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	A-Coded

Downloaded from Arrow.com.

LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	315.100/g
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	18

Downloaded from Arrow.com.