molex



Part Number : 430311001
Product Description : Micro-Fit 3.0 First Mate/Last Break Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 24-20 AWG, Reel
Series Number : 43031
Status : Active
Product Category : Crimp Terminals

Documents and Resources

Drawings

430311001_sd.pdf

430311001-PK-000.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

430450001-AS-000.pdf

PS-43045-001.pdf

430450005-TS-000.pdf

430450007-TS-000.pdf

TS-43045-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	43031
Description	Micro-Fit 3.0 First Mate/Last Break Crimp Terminal, Male, with Tin (Sn) Plated Phosphor Bronze Contact, 24-20 AWG, Reel
Application	Wire-to-Wire
Product Name	Micro-Fit FMLB
UPC	198282802051

Electrical

Current - Maximum per Contact	7.0A

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin

Downloaded from Arrow.com.

Net Weight	0.100/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size (AWG)	20, 22, 24
Wire Size mm^2	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Plug Housings	43020
Micro-Fit 3.0 Single Row Plug Housings	43640

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	11030043
FineAdjust Applicator for Insulation OD 1.30-1.85mm, 24-20 AWG Wire	639004500
FineAdjust Applicator for Insulation OD 1.10-1.30mm - 24-20 AWG	639018800
FineAdjust Applicator for Micro-Fit 3.0 Terminals, for 24-20 AWG Wire with Insulation Diameter 0.91-1.09mm	639018900
Hand Crimp Tool for Micro-Fit 3.0 Male Crimp Terminals, FMLB, 24-20 AWG, UL 1007 Wires	2238635200

Downloaded from Arrow.com.

Downloaded from Arrow.com.