



TLS 2200®/TLS PC Link™ Labels

TLS 2200®/TLS PC Link™ Label Index By Size (Continued)

Diagram	Catalog Number	Labels Per Roll	Material	Color	B-Number	Label Width Inch (mm) A	Label Height Inch (mm) B	Write-On Height Inch (mm) C	Wire Gauge
1.900" (Continued)									
Fig. 8	PTL-43-439-BL	Continuous	Vinyl	Blue	B-439	1.900 (48.3)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-43-439-GR	Continuous	Vinyl	Green	B-439	1.900 (48.3)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-43-439-OR	Continuous	Vinyl	Orange	B-439	1.900 (48.3)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-43-439-RD	Continuous	Vinyl	Red	B-439	1.900 (48.3)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-43-439-YL	Continuous	Vinyl	Yellow	B-439	1.900 (48.3)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-43-483	Continuous	Polyester	White	B-483	1.900 (48.3)	50 ft. (15.2 m)	—	—
Fig. 8	PTL-43-489	Continuous	Polyester	White	B-489	1.900 (48.3)	50 ft. (15.2 m)	—	—
1.930"									
Fig. 6	PTL-161-499	100	Nylon	White	B-499	1.930 (49.0)	3.000 (76.2)	—	—
1.938"									
Fig. 31	PTL-40-412	750	Polypropylene	White	B-412	1.938 (49.2)	0.375 (9.5)	—	—
Fig. 31	BPTL-40-412	5000	Polypropylene	White	B-412	1.938 (49.2)	0.375 (9.5)	—	—
Fig. 7	PTL-66-427	100	Vinyl	White	B-427	1.938 (49.2)	3.150 (80)	1.000 (25.4)	Cables
Fig. 7	PTL-66-427	100	Vinyl	White	B-427	1.938 (49.2)	3.150 (80)	1.000 (25.4)	—
2.000"									
Fig. 4	PTL-2-423	100	Polyester	White	B-423	2.000 (50.8)	0.250 (6.4)	—	—
Fig. 4	PTL-2-426	100	Polyimide	Amber	B-426	2.000 (50.8)	0.250 (6.4)	—	—
Fig. 4	PTL-2-477	100	Polyimide	White	B-477	2.000 (50.8)	0.250 (6.4)	—	—
Fig. 4	PTL-2-457	100	Polyimide	White	B-457	2.000 (50.8)	0.250 (6.4)	—	—
Fig. 4	PTL-2-478	100	Polyimide	White	B-478	2.000 (50.8)	0.250 (6.4)	—	—
Fig. 4	PTL-2-479	100	Polyimide	White	B-479	2.000 (50.8)	0.250 (6.4)	—	—
Fig. 4	PTL-61-483	100	Polyester	White	B-483	2.000 (50.8)	0.500 (12.7)	—	—
Fig. 4	PTL-20-424	100	Paper	White	B-424	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	BPTL-20-424	1000	Paper	White	B-424	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	PTL-20-435	100	Polyester	Silver	B-435	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	PTL-20-483	100	Polyester	White	B-483	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	PTL-20-486	100	Polyester	Silver	B-486	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	PTL-20-489	100	Polyester	White	B-489	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 16	PTPSL-20-428	100	Polyester	Silver	B-428	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 16	PTPSL-20-424	100	Paper	White	B-424	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 16	PTPSL-20-422	100	Polyester	White	B-422	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	PTL-20-7576	100	Polyester	Silver	B-7576	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	PTL-20-7546	100	Polyester	White	B-7546	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	PTL-20-352	100	Vinyl	Silver	B-352	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	PTL-20-351	100	Vinyl	White	B-351	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	PTL-20-422	100	Polyester	White	B-422	2.000 (50.8)	1.000 (25.4)	—	—
Fig. 4	BPTL-20-422	1000	Polyester	White	B-422	2.000 (50.8)	1.000 (25.4)	—	—

