



## Technical Data

08.03.2021

TFE4 - 4:1 shrink ratio  
Heat shrinkable tubing - PTFE

**TFE4-3/8**

**Article Number 339-00959**



Material: Polytetrafluoroethylene (PTFE)

Colour: Transparent (CL)

Supplied Ø D min.: 9.52 mm

Recov. Ø d max.: 2.44 mm

Wall (WT): 0.30 mm

Shrink Ratio: 4:1

Longitudinal Change After Shrinkage: -20 % max.

Min. Shrink Temperature - °C: +330 °C

Test Method


Flammability: non-burning

Operating Temperature - °C: -65 °C to +260 °C

Dielectric Strength: 40 kV/mm

DIN 53481

Tensile Strength: 39 MPa



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved