

Representative Image

Catalog No. G972

Description: NON-INS TUB RING 2/2AN 5/16

UPC No 786210812533

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Non-Insulated Tubular Ring Terminal, Length 1.59 Inches, Width .69 Inches, Bolt Hole 5/16 Inch, Wire Range 2/2AN, Copper, Tin Plated, 100 Pack

Descriptors

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indentor or double indentor (recommended for solid wire).

Specifications

Voltage Rating	600 V
Material	Copper
Color	Metallic

Classifications

Brand Name	Sta-Kon
Standard	UL E9809

Dimensions

Wire Size	2 AWG

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant
POPs	POPs 28 Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	180° (horizontal)
Slender flange model	N
Insulated	N

by ABB

Downloaded from Arrow.com.

ETIM	EC001051 Tube cable lug for copper conductors
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of mounting holes	1

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	N/A	N/A
CSA	7222	622302	N/A	N/A	N/A
UL	E9809	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.